

Garant
Short drill chuck Form AD/B, SK 40, Clamping range: 0,3-10mm

Order data

Order number	301465 0,3-10
GTIN	4045197868787
Item class	31B

Description
Version:

For clockwise and anticlockwise rotation.

With Balluff/RFID chip bore. Maximum radial run-out $\leq 20 \mu\text{m}$.

Glass bead blasted. Slim design for the most popular \varnothing up to 10.2 mm.

Supplied with:

Clamping wrench with T-handle.

Optional extras:

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

Technical description

External \varnothing D	38 mm
Spare chuck key No. 627425	4 AF
Overhang dimension A	73 mm
Clamping range	0.3 - 10.2 mm
Type	slim
Adapter	SK 40
Arbor standard	ISO 7388-1
Shape	ADB
Through-coolant	yes, with max. 50 bar

Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 20 μm
maximum tightening torque $M_{d\max}$	≤ 14 Nm
Type of product	Short drill chuck

Accessories

Pull studForm B suitable for steep tapers 40	308640 40
Pull studForm A suitable for steep tapers 40	308600 40
Pull studsealed suitable for steep tapers 40	308635 40
Wrench for pull studsISO 7388 suitable for ISO taper size 40	308830 40
Pull stud 45°sealed suitable for steep tapers 40	308760 40
Special pull stud with internal thread suitable for steep tapers 40	308740 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
Pull studsealed, form B suitable for steep tapers 40	308650 40
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
Pull stud, 18CrNiMo7Form A suitable for steep tapers 40	308605 40
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 40	308615 40
Pull stud 60°sealed suitable for steep tapers 40	308785 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308630 40
Pull studsealed suitable for steep tapers 40	308660 40
Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40	308801 40
Pull studsealed, form A suitable for steep tapers 40	308610 40

Pull studsealed, form B suitable for steep tapers 40	308620 40
Pull stud 90°sealed suitable for steep tapers 40	308795 40
Pull studMazak, form A suitable for steep tapers 40M	308670 40M
Pull stud 90°sealed suitable for steep tapers 40	308790 40
Pull stud 45°sealed suitable for steep tapers 40	308765 40
Special pull stud with no internal threadsealed suitable for steep tapers 40	308700 40
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40