

**Hammer drill, Type: GBH228F****Order data**

Order number	075510 GBH228F
GTIN	3165140843669
Item class	03B

Description**Version:**

Sturdy hammer drill with **SDS-plus arbor** and high drill feed rate.

- **Overload clutch to protect both user and machine.**
- **Stepless speed control for responsive starts to drilling.**
- **Versatile application possibilities using the chisel function (zero rotation).**
- **Reversible, for releasing jammed drills.**
- **Exchange chuck for quick changeover between hammer drilling in concrete and hammer-free drilling in wood and steel.**
- **Impact action can be switched off for drilling in wood and steel.**
- **Active vibration damping for 27 % less vibration than its predecessor model.**

Advantage:

Impact energy 3.2 Joules.

Supplied with:

With additional handle, machine cloth. Supplied with 13mm quick-change chuck, SDS chuck, 210 mm depth stop, L-BOXX 136.

Note:

Suitable carbide hammer drills can be found from No. 787000. Suitable spare batteries and chargers can be found under No. 073851 – 073866.

Technical description

maximum twist drill size Ø in wood	30 mm
------------------------------------	-------

maximum twist drill size Ø in concrete	28 mm
maximum vibration to EN	11 m/s ²
Manufacturer's designation	GBH 2-28 F
Tool arbor shape	SDS-Plus
Weight	3.1 kg
Power consumption	880 W
Impact energy	3.2 J
maximum twist drill size Ø in steel	13 mm
maximum hammer rate	4000 min ⁻¹
Shank	SDS Plus
Packaging	Modular case (L-Boxx)
Power supply	Mains operated
Suitable for material	Concrete
Suitable for material	Steel
Suitable for material	Stone
Suitable for material	Masonry
Type of product	Hammer drill

Accessories

Carbide-tipped multi-purpose drill Drill Ø 8 mm	787040 8
Carbide-tipped multi-purpose drill setlong Drill Ø 6-12 mm	787055 6-12
Carbide-tipped multi-purpose drill long Drill Ø 6 mm	787045 6
Carbide-tipped multi-purpose drill bit, 1/4 inch (E 6.3) Drill Ø 6 mm	787047 6
Carbide-tipped multi-purpose drill Drill Ø 4 mm	787040 4
Carbide-tipped multi-purpose drill bit, 1/4 inch (E 6.3) Drill Ø 8 mm	787047 8
Carbide-tipped multi-purpose drill Drill Ø 6 mm	787040 6

Carbide-tipped multi-purpose drill long Drill Ø 12 mm	787045 12
Carbide-tipped multi-purpose drill long with SDS-plus shank socket Drill Ø 10 mm	787060 10
Carbide-tipped multi-purpose drill long Drill Ø 8 mm	787045 8
Carbide-tipped multi-purpose drill bit, 1/4 inch (E 6.3) Drill Ø 10 mm	787047 10
Carbide-tipped multi-purpose drill Drill Ø 10 mm	787040 10
Carbide-tipped multi-purpose drill long Drill Ø 10 mm	787045 10
Carbide-tipped multi-purpose drill Drill Ø 12 mm	787040 12
Carbide-tipped multi-purpose drill bit, 1/4 inch (E 6.3) Drill Ø 4 mm	787047 4
Carbide-tipped multi-purpose drill Drill Ø 5 mm	787040 5
Carbide-tipped multi-purpose drill long with SDS-plus shank socket Drill Ø 8 mm	787060 8
Carbide-tipped multi-purpose drill set Drill Ø 4-10 mm	787050 4-10
Carbide-tipped multi-purpose drill bit set, 1/4 inch (E 6.3) Drill Ø 4-10 mm	787057 4-10
Carbide-tipped multi-purpose drill long with SDS-plus shank socket Drill Ø 12 mm	787060 12
Carbide-tipped multi-purpose drill bit, 1/4 inch (E 6.3) Drill Ø 5 mm	787047 5