

Garant
Burr Z9 – very coarse (non-ferrous / aluminium), Carbide, Type: C1225

Order data

Order number	543709 C1225
GTIN	4045197522351
Item class	51D

Description
Version:

Extra sturdy shank with \varnothing 8 mm.

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Cylindrical ball nose shape** (WRC)

Application:

For the most demanding burring operations.

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

Shape description	ball nose
Overall length	65 mm
Toothing grit designation	very coarse (NF/Alu)
Head \varnothing	12 mm
Tooth type abbreviation	Z9
Shape	C1225
Shank \varnothing	8 mm
Head length	25 mm
Series	Tooth configuration Z9

Tool material	Carbide
Type of product	Burr

User data

	Suitability	V_c	ISO code
Alu Mg	suitable		
CuZn	suitable		
Plastic, GRP	suitable only under restricted conditions		