

Garant**Grinding disc (CER), Ø 76.2 mm, Grit: 36****Order data**

Order number	554013 36
GTIN	4045197526021
Item class	51E

Description**Version:**

The Roloc™, Combidisc® CDR **quick-change system** with a plastic thread permits safe abrasive tool changing “with a single twist of the wrist” in a very short time.

Very high material removal rate and service life due to the use of self-sharpening ceramic grit (CER).

Application:

Use in conjunction with hard support pad No. 554089.

For efficient abrasion of small areas, even with changing contours. Reduced tool changing times save costs on multi-stage operations.

Note:

Roloc™ bristle discs can be found from No. 573510 onwards.

Technical description

Grit	36
Disc Ø	76.2 mm
Grinding media	Ceramic grit

Grinding medium code	Ceramic
Grinding media backing	Fibre underlay
Product name attribute	Ø 76.2 mm
maximum speed	20000 min ⁻¹
Type of product	Grinding wheel

User data

	Suitability	V _c	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
CuZn	suitable		
dry	suitable		

Accessories

Rubber backing pad shank Ø 6 mmsoft External Ø 75 mm	554091 75
Rubber backing pad with mounting M14hard External Ø 75 mm	554088 75
Rubber backing pad shank Ø 6 mmhard External Ø 75 mm	554089 75
Plastic backing pad shank Ø 6 mm External Ø 75 mm	554090 75
	554093 75

Rubber backing pad shank \varnothing 6 mm medium hard External
 \varnothing 75 mm

Rubber backing pad shank \varnothing 6 mm medium External \varnothing 75
mm

554092 75

Rubber backing pad with M14 mounting hard External \varnothing
75 mm

554094 75