

Garant**Burr Z9 – very coarse (non-ferrous / aluminium), Carbide, Type: F1225****Order data**

| | |
|--------------|---------------|
| Order number | 543709 F1225 |
| GTIN | 4045197522382 |
| Item class | 51D |

Description**Version:**

Extra sturdy shank with \varnothing 8 mm.

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Round arch shape** (RBF).

Application:

For the most demanding burring operations.

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

| | |
|---------------------------|------------------------|
| Shape description | round arch |
| Shape | F1225 |
| Overall length | 65 mm |
| Head \varnothing | 12 mm |
| Toothing grit designation | very coarse (NF/Alu) |
| Tooth type abbreviation | Z9 |
| Shank \varnothing | 8 mm |
| Head length | 25 mm |
| Series | Tooth configuration Z9 |

| | |
|-----------------|---------|
| Tool material | Carbide |
| Type of product | Burr |

User data

| | Suitability | V_c | ISO code |
|--------------|---|----------------------|-----------------|
| Alu Mg | suitable | | |
| CuZn | suitable | | |
| Plastic, GRP | suitable only under restricted conditions | | |