

**Garant****Burr Z9 – very coarse (non-ferrous / aluminium), Carbide, Type: L1230****Order data**

Order number	543709 L1230
GTIN	4045197522405
Item class	51D

**Description****Version:**

Extra sturdy shank with  $\varnothing$  8 mm.

**GARANT** burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Round cone shape** (KEL).

**Application:**

For the most demanding burring operations.

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

**Technical description**

Shape	L1230
Overall length	70 mm
Head $\varnothing$	12 mm
Toothing grit designation	very coarse (NF/Alu)
Tooth type abbreviation	Z9
Shape description	round cone
Shank $\varnothing$	8 mm
Head length	30 mm
Series	Tooth configuration Z9

Tool material	Carbide
Type of product	Burr

**User data**

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
Alu Mg	suitable		
CuZn	suitable		
Plastic, GRP	suitable only under restricted conditions		