

Garant

Mini burr Z7 – medium, diamond cut, Carbide, Type: AS0210



Order data

Order number	546900 AS0210
GTIN	4045197156716
Item class	51D

Description

Version:

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide.

Carbide mini burr with shank \varnothing 3 mm. **Cylindrical shape AS (ZYAS), with end cut.**

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

Shape description	Cylindrical with end cut
Type of cut	staggered teeth
Overall length	40 mm
Head \varnothing	2 mm
Tooth type abbreviation	Z7
Shape	AS0210
Toothing grit designation	medium
Shank \varnothing	3 mm
Head length	10 mm
Series	Tooth configuration Z7
Tool material	Carbide

Type of product

Burr

User data

	Suitability	V_c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
Uni	suitable		