

Threads "Go" ring gauge 6g, Thread: M18



Order data

Order number	486010 M18
GTIN	2050001037206
Item class	48B

Description

Version:

The ground first thread pitch removes coarse swarf in the component and prevents premature fracture of the first thread pitch. Version to DIN 2279 - 2299.

Application:

For metric ISO threads, right-hand DIN 13.

Standard:

Toleranzen und Abmaße nach **DIN ISO 1502**.

Note:

Thread gauges for threads with other pitches, Whitworth, trapezoidal, round, UNC, UNF, NPT, and LH threads available on request.

Technical description

Tolerance class	6g
Thread	M18
Thread pitch	2.5 mm
Calibration	L12

Type of gauge	"Go" plug gauge
Tolerance zone	g
Standard	DIN 13
Thread type	M
Quality	6
Type of product	Thread "Go" ring gauge

Services

DAkkS calibration Thread "Go" ring gauge maximum \varnothing 100 mm	028640 100
Calibration Thread ring gauge maximum \varnothing 20 mm	028600 20