

Garant**Mini burr set, 10 pieces Z7 – medium, diamond cut, Carbide****Order data**

Order number	546940
GTIN	4045197156938
Item class	51D

Description**Version:**

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide.

Assortment of mini burrs in the most popular shapes and sizes. Shank \varnothing 3 mm.

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Supplied with:

1 pc. each No. 546900 size AS0313; AS0613; C0313; C0613; D0302; D0605; F0313; G0313; G0613; M0613.

Technical description

Tooth type abbreviation	Z7
Type of cut	staggered teeth

Toothing grit designation	medium
Series	Tooth configuration Z7
Tool material	Carbide
Shank Ø	3 mm
Number of burrs	10
Type of product	Burr

Accessories

Mini burrZ7 – medium, diamond cut Type G0313	546900 G0313
Mini burrZ7 – medium, diamond cut Type C0313	546900 C0313
Mini burrZ7 – medium, diamond cut Type F0313	546900 F0313
Mini burrZ7 – medium, diamond cut Type D0605	546900 D0605
Mini burrZ7 – medium, diamond cut Type AS0313	546900 AS0313
Mini burrZ7 – medium, diamond cut Type C0613	546900 C0613
Mini burrZ7 – medium, diamond cut Type AS0613	546900 AS0613
Mini burrZ7 – medium, diamond cut Type M0613	546900 M0613
Mini burrZ7 – medium, diamond cut Type D0302	546900 D0302
Mini burrZ7 – medium, diamond cut Type G0613	546900 G0613