

Garant**Mini burr Z FINE – very fine, Carbide, Type: C0313****Order data**

Order number	546840 C0313
GTIN	4045197679857
Item class	51D

Description**Version:**

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide.

Carbide mini burr with shank \varnothing 3 mm. **Cylindrical ball nose shape** (WRC)

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

Shape	C0313
Tooth type abbreviation	Z FINE
Toothing grit designation	very fine
Head \varnothing	3 mm

Shape description	Ball nose
Overall length	40 mm
Shank Ø	3 mm
Head length	13 mm
Series	Tooth configuration Z FINE
Tool material	Carbide
Type of product	Burr

User data

	Suitability	V _c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		