

Threads "Go" plug gauge, Thread: M48



Order data

Order number	486020 M48
GTIN	4045197213136
Item class	48B

Description

Version:

The ground first thread pitch removes coarse swarf in the component and prevents premature fracture of the first thread pitch. Version to DIN 2279 - 2299.

"Go" and "No Go" gauges are separate (DIN 2240, part 2, form GE).

Application:

For metric ISO threads, right-hand DIN 13.

Tolerance class 6H (up to M 1.4 = 5H).

Standard:

Toleranzen und Abmaße nach **DIN ISO 1502**.

Note:

Thread gauges for threads with other pitches, Whitworth, trapezoidal, round, UNC, UNF, NPT, and LH threads available on request.

Calibration: L11

Standard: DIN 13

Thread type: M

Thread pitch: 5 mm

Technical description

Tolerance class	6H
Thread pitch	5 mm
Thread	M48
Tolerance zone	H
Standard	DIN 13

Thread type	M
Quality	6
Type of gauge	"Go" plug gauge
Calibration	L11
Type of product	Thread Go plug gauge

Services

Calibration "Go" / "No Go" thread plug gauge maximum Ø 60 mm	018580 60
Labelling laser-etched Type	018940
DAkkS calibration "Go" / "No Go" thread plug gauge maximum Ø 90 mm	019580 90
Calibration "Go" / "No Go" thread plug gauge maximum Ø 60 mm	028500 60
DAkkS calibration "Go" / "No Go" thread plug gauge maximum Ø 90 mm	028540 90