

## Threads "No Go" ring gauge 6g, Thread: M24



### Order data

|              |               |
|--------------|---------------|
| Order number | 486050 M24    |
| GTIN         | 2050001037404 |
| Item class   | 48B           |

### Description

**Version:**

The ground first thread pitch removes coarse swarf in the component and prevents premature fracture of the first thread pitch. Version to DIN 2279 - 2299.

**Application:**

For metric ISO threads, right-hand DIN 13.

**Standard:**

Toleranzen und Abmaße nach **DIN ISO 1502**.

**Note:**

Thread gauges for threads with other pitches, Whitworth, trapezoidal, round, UNC, UNF, NPT, and LH threads available on request.

### Technical description

|                 |      |
|-----------------|------|
| Tolerance class | 6g   |
| Thread pitch    | 3 mm |
| Thread          | M24  |
| Calibration     | L12  |

|                 |                           |
|-----------------|---------------------------|
| Type of gauge   | "No Go" gauge             |
| Tolerance zone  | g                         |
| Standard        | DIN 13                    |
| Thread type     | M                         |
| Quality         | 6                         |
| Type of product | Thread "No Go" ring gauge |

### Services

|   |            |
|---|------------|
| Calibration Thread ring gauge maximum $\varnothing$ 60 mm             | 028600 60  |
| DAkkS calibration Thread "Go" ring gauge maximum $\varnothing$ 100 mm | 028640 100 |