

Garant**Mini burr Z7 – medium, diamond cut, Carbide, Type: C0613****Order data**

Order number	546900 C0613
GTIN	4045197156761
Item class	51D

Description**Version:**

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide.

Carbide mini burr with shank \varnothing 3 mm. **Cylindrical ball nose shape** (WRC)

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

Overall length	43 mm
Shape description	Ball nose
Tooth type abbreviation	Z7
Type of cut	staggered teeth
Shape	C0613
Head \varnothing	6 mm
Toothing grit designation	medium
Shank \varnothing	3 mm
Head length	13 mm
Series	Tooth configuration Z7

Tool material	Carbide
Type of product	Burr

User data

	Suitability	V_c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
Uni	suitable		