

## Threads "No Go" ring gauge 6g, Thread: M33



### Order data

Order number	486050 M33
GTIN	2050001039927
Item class	48B

### Description

**Version:**

The ground first thread pitch removes coarse swarf in the component and prevents premature fracture of the first thread pitch. Version to DIN 2279 - 2299.

**Application:**

For metric ISO threads, right-hand DIN 13.

**Standard:**

Toleranzen und Abmaße nach **DIN ISO 1502**.

**Note:**

Thread gauges for threads with other pitches, Whitworth, trapezoidal, round, UNC, UNF, NPT, and LH threads available on request.

### Technical description

Thread pitch	3.5 mm
Thread	M33
Tolerance class	6g
Calibration	L12

Tolerance zone	g
Type of gauge	"No Go" gauge
Standard	DIN 13
Thread type	M
Quality	6
Type of product	Thread "No Go" ring gauge

### Services

DAkkS calibration Thread "Go" ring gauge maximum $\varnothing$ 100 mm	028640 100
Calibration Thread ring gauge maximum $\varnothing$ 60 mm	028600 60