

Threads "Go" / "No Go" plug gauge, Thread: M33



Order data

| | |
|--------------|---------------|
| Order number | 486000 M33 |
| GTIN | 4045197213105 |
| Item class | 48B |

Description

Version:

The ground first thread pitch removes coarse swarf in the component and prevents premature fracture of the first thread pitch. Version to DIN 2279 - 2299.

"Go" and "No Go" ends on a single handle (DIN 2240, part 1, form R). "No Go" end marked red.

Application:

For metric ISO threads, right-hand DIN 13.

Tolerance class 6H (up to M 1.4 = 5H).

Standard:

Toleranzen und Abmaße nach **DIN ISO 1502**.

Note:

Thread gauges for threads with other pitches, Whitworth, trapezoidal, round, UNC, UNF, NPT, and LH threads available on request.

Technical description

| | |
|-----------------|---------------|
| Thread | M33 |
| Thread pitch | 3.5 mm |
| Tolerance class | 6H |
| Standard | DIN 13 |
| Thread type | M |
| Quality | 6 |
| Tolerance zone | H |
| Type of gauge | "No Go" gauge |

| | |
|-----------------|-----------------------------|
| Type of gauge | "Go" plug gauge |
| Calibration | L10 |
| Type of product | Thread Go / NoGo plug gauge |

Services

| | |
|--|-----------|
| CalibrationGo / No Go thread plug gauge maximum Ø 60 mm | 028550 60 |
| DAkkS calibration "Go" / "No Go" thread plug gauge maximum Ø 90 mm | 028590 90 |