

Thread "Go" / "No Go" plug gauge set, Set contents: M3-M12**Order data**

Order number	486040 M3-M12
GTIN	4045197295675
Item class	48B

Description**Version:**

"Go" and "No Go" ends on a single handle (DIN 2240, part 1 form S). "No Go" end marked red.

Standard:

Toleranzen und Abmaße nach **DIN 13 Blatt 16 und 17.**

Content:

1x each thread plug gauge No. 486000
M3, M4, M5, M6, M8, M10, M12.

Supplied with:

Strong wooden box with protective foam cushion.

Optional extras:

Core hole plug gauge No. 486055.

Note:

Thread gauges for fine threads with other pitches, Whitworth, trapezoidal, round, UNC, UNF and NPT thread and left hand threads available on request.

Technical description

Set contents	M3-M12
Standard	DIN 13

Thread type	M
Packaging	sturdy box
Calibration	S13
Type of product	Thread Go / NoGo plug gauge

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/486040-M3-M12>