

## Threads "Go" ring gauge 6g, Thread: M10



### Order data

Order number	486010 M10
GTIN	2050001037169
Item class	48B

### Description

**Version:**

The ground first thread pitch removes coarse swarf in the component and prevents premature fracture of the first thread pitch. Version to DIN 2279 - 2299.

**Application:**

For metric ISO threads, right-hand DIN 13.

**Standard:**

Toleranzen und Abmaße nach **DIN ISO 1502**.

**Note:**

Thread gauges for threads with other pitches, Whitworth, trapezoidal, round, UNC, UNF, NPT, and LH threads available on request.

### Technical description

Thread	M10
Tolerance class	6g
Thread pitch	1.5 mm
Calibration	L12

Tolerance zone	g
Type of gauge	"Go" plug gauge
Standard	DIN 13
Thread type	M
Quality	6
Type of product	Thread "Go" ring gauge

### Services

DAkkS calibration Thread "Go" ring gauge maximum $\varnothing$ 100 mm	028640 100
Calibration Thread ring gauge maximum $\varnothing$ 20 mm	028600 20