

Threads "No Go" ring gauge 6g, Thread: M12



Order data

Order number	486050 M12
GTIN	2050001037343
Item class	48B

Description

Version:

The ground first thread pitch removes coarse swarf in the component and prevents premature fracture of the first thread pitch. Version to DIN 2279 - 2299.

Application:

For metric ISO threads, right-hand DIN 13.

Standard:

Toleranzen und Abmaße nach **DIN ISO 1502**.

Note:

Thread gauges for threads with other pitches, Whitworth, trapezoidal, round, UNC, UNF, NPT, and LH threads available on request.

Standard: DIN 13

Thread type: M

Calibration: L12

Thread pitch: 1.75 mm

Technical description

Thread	M12
Tolerance class	6g

Thread pitch	1.75 mm
Calibration	L12
Tolerance zone	g
Type of gauge	"No Go" gauge
Standard	DIN 13
Thread type	M
Quality	6
Type of product	Thread "No Go" ring gauge

Services

Calibration Thread ring gauge maximum \varnothing 20 mm	018610 20
Labelling laser-etched Type	018940
DAkkS calibration Thread "Go" ring gauge maximum \varnothing 100 mm	019610 100
Calibration Thread ring gauge maximum \varnothing 20 mm	028600 20
DAkkS calibration Thread "Go" ring gauge maximum \varnothing 100 mm	028640 100