

**Garant**
**Mini burr Z7 – medium, diamond cut, Carbide, Type: M0311**

**Order data**

Order number	546900 M0311
GTIN	4045197156907
Item class	51D

**Description**
**Version:**

**GARANT** burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide.

Carbide mini burr with shank  $\varnothing$  3 mm.

**Application:**

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

**Technical description**

Shape	M0311
Tooth type abbreviation	Z7
Toothing grit designation	medium
Shape description	pointed cone
Type of cut	staggered teeth
Head $\varnothing$	3 mm
Overall length	40 mm
Shank $\varnothing$	3 mm
Head length	11 mm
Series	Tooth configuration Z7
Tool material	Carbide

Type of product

Burr

**User data**

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
Uni	suitable		