

Threads "Go" / "No Go" plug gauge, Thread: M14



Order data

Order number	486000 M14
GTIN	2050001690982
Item class	48B

Description

Version:

The ground first thread pitch removes coarse swarf in the component and prevents premature fracture of the first thread pitch. Version to DIN 2279 - 2299.

"Go" and "No Go" ends on a single handle (DIN 2240, part 1, form R). "No Go" end marked red.

Application:

For metric ISO threads, right-hand DIN 13.

Tolerance class 6H (up to M 1.4 = 5H).

Standard:

Toleranzen und Abmaße nach **DIN ISO 1502**.

Note:

Thread gauges for threads with other pitches, Whitworth, trapezoidal, round, UNC, UNF, NPT, and LH threads available on request.

Technical description

Thread pitch	2 mm
Tolerance class	6H
Thread	M14
Thread type	M
Standard	DIN 13
Tolerance zone	H
Quality	6
Type of gauge	"No Go" gauge

Type of gauge	"Go" plug gauge
Calibration	L10
Type of product	Thread Go / NoGo plug gauge

Services

CalibrationGo / No Go thread plug gauge maximum Ø 20 mm	028550 20
DAkkS calibration "Go" / "No Go" thread plug gauge maximum Ø 90 mm	028590 90