

Threads "Go" ring gauge 6g, Thread: M36



Order data

Order number	486010 M36
GTIN	2050001669919
Item class	48B

Description

Version:

The ground first thread pitch removes coarse swarf in the component and prevents premature fracture of the first thread pitch. Version to DIN 2279 - 2299.

Application:

For metric ISO threads, right-hand DIN 13.

Standard:

Toleranzen und Abmaße nach **DIN ISO 1502**.

Note:

Thread gauges for threads with other pitches, Whitworth, trapezoidal, round, UNC, UNF, NPT, and LH threads available on request.

Technical description

Thread	M36
Thread pitch	4 mm
Tolerance class	6g
Calibration	L12

Tolerance zone	g
Type of gauge	"Go" plug gauge
Thread type	M
Standard	DIN 13
Quality	6
Type of product	Thread "Go" ring gauge

Services

DAkkS calibration Thread "Go" ring gauge maximum \varnothing 100 mm	028640 100
Calibration Thread ring gauge maximum \varnothing 60 mm	028600 60