

Threads "No Go" ring gauge 6g, Thread: M2,5



Order data

Order number	486050 M2,5
GTIN	2050001037268
Item class	48B

Description

Version:

The ground first thread pitch removes coarse swarf in the component and prevents premature fracture of the first thread pitch. Version to DIN 2279 - 2299.

Application:

For metric ISO threads, right-hand DIN 13.

Standard:

Toleranzen und Abmaße nach **DIN ISO 1502**.

Note:

Thread gauges for threads with other pitches, Whitworth, trapezoidal, round, UNC, UNF, NPT, and LH threads available on request.

Technical description

Thread pitch	0.45 mm
Tolerance class	6g
Thread	M2.5
Calibration	L12

Tolerance zone	g
Type of gauge	"No Go" gauge
Thread type	M
Standard	DIN 13
Quality	6
Type of product	Thread "No Go" ring gauge

Services

DAkkS calibration Thread "Go" ring gauge maximum \varnothing 100 mm	028640 100
Calibration Thread ring gauge maximum \varnothing 3 mm	028600 3