

## Threads "Go" / "No Go" plug gauge, TiN, Thread: M3



### Order data

Order number	486008 M3
GTIN	2050001060419
Item class	48B

### Description

#### Version:

The ground first thread pitch removes coarse swarf in the component and prevents premature fracture of the first thread pitch. Version to DIN 2279 - 2299.

**"Go" and "No Go" ends on a single handle (DIN 2240, part 1, form R).** "No Go" end marked red.

"Go" end TiN coated, resulting in longer working life, dirt trap groove from M6.

#### Application:

For metric ISO threads, right-hand DIN 13.

Tolerance class 6H (up to M 1.4 = 5H).

#### Standard:

Toleranzen und Abmaße nach **DIN ISO 1502**.

#### Optional extras:

Core hole plug gauge No. 486055.

#### Note:

Thread gauges for threads with other pitches, Whitworth, trapezoidal, round, UNC, UNF, NPT, and LH threads available on request.

### Technical description

Thread	M3
Thread pitch	0.5 mm
Tolerance class	6H
Thread type	M
Standard	DIN 13
Quality	6

Tolerance zone	H
Type of gauge	"No Go" gauge
Type of gauge	"Go" plug gauge
Surface "OK" side	TiN
Calibration	L10
Type of product	Thread Go / NoGo plug gauge

### Services

CalibrationGo / No Go thread plug gauge maximum $\varnothing$ 3 mm	028550 3
DAkkS calibration "Go" / "No Go" thread plug gauge maximum $\varnothing$ 90 mm	028590 90