

Threads "Go" ring gauge 6g, Thread: M2



Order data

Order number	486010 M2
GTIN	2050001037084
Item class	48B

Description

Version:

The ground first thread pitch removes coarse swarf in the component and prevents premature fracture of the first thread pitch. Version to DIN 2279 - 2299.

Application:

For metric ISO threads, right-hand DIN 13.

Standard:

Toleranzen und Abmaße nach **DIN ISO 1502**.

Note:

Thread gauges for threads with other pitches, Whitworth, trapezoidal, round, UNC, UNF, NPT, and LH threads available on request.

Technical description

Tolerance class	6g
Thread pitch	0.4 mm
Thread	M2
Calibration	L12

Type of gauge	"Go" plug gauge
Tolerance zone	g
Standard	DIN 13
Thread type	M
Quality	6
Type of product	Thread "Go" ring gauge

Services

Calibration Thread ring gauge maximum \varnothing 3 mm	028600 3
--	----------