

**Flap wheel (A), 60 grit, Head Ø×head width: 40X15mm****Order data**

Order number	554100 40X15
GTIN	4045197235466
Item class	52E

Description**Version:**

Flap strips bonded on to the shank of the tool.

Abrasive strips covered with **Aluminium Oxide (A)**.

Application:

Primarily for finish grinding and polishing tasks on larger radii in tool and mould making, for vessel and machine fabrication. The abrasive strips adapt to the contours of the component.

Technical description

Head width	15 mm
Grit	60
maximum speed	19100 min ⁻¹
recommended speed	12000 min ⁻¹
Shank Ø	6 mm
Head Ø	40 mm
Grinding media	Aluminium Oxide grit (A)
Grinding medium code	A

Product name attribute	60 grit
Type of product	Flap wheel

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable only under restricted conditions		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
dry	suitable		