



## Burr Tooth profile INOX – coarse, Carbide, Type: A1020



### Order data

Order number	547200 A1020
GTIN	4007220952252
Item class	55F

### Description

#### Version:

**The innovative tooth geometry** permits **very high metal removal rates** combined with **smooth cutting and good guidance accuracy**. Outstanding chip formation and surface results, low heat input into the material (no tempering colouration). Shank  $\varnothing$  6mm.

#### Application:

Optimised for use on **austenitic, rust-resistant and acid-resistant steels**, soft titanium alloys and non-ferrous metals.

### Technical description

Toothing grit designation	coarse
Shape	A1020
Head $\varnothing$	10 mm
Overall length	60 mm
Shape description	Cylindrical
Tooth type abbreviation	INOX
Shank $\varnothing$	6 mm
Head length	20 mm
Tool material	Carbide
Type of product	Burr

### User data

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
Alu Mg	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable only under restricted conditions		
CuZn	suitable only under restricted conditions		