

**Burr Tooth profile INOX – coarse, Carbide, Type: A1225****Order data**

Order number	547200 A1225
GTIN	4007220900505
Item class	55F

**Description****Version:**

**The innovative tooth geometry** permits **very high metal removal rates** combined with **smooth cutting and good guidance accuracy**. Outstanding chip formation and surface results, low heat input into the material (no tempering colouration). Shank  $\varnothing$  6mm.

**Application:**

Optimised for use on **austenitic, rust-resistant and acid-resistant steels**, soft titanium alloys and non-ferrous metals.

**Technical description**

Shape description	cylindrical
Tooth type abbreviation	INOX
Shape	A1225
Toothing grit designation	coarse
Head $\varnothing$	12 mm
Overall length	65 mm
Shank $\varnothing$	6 mm
Head length	25 mm
Tool material	Carbide
Type of product	Burr

**User data**

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
Alu Mg	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable only under restricted conditions		
CuZn	suitable only under restricted conditions		