



Burr Tooth configuration STEEL – coarse, Carbide, Type: C0820



Order data

Order number	547100 C0820
GTIN	4007220937150
Item class	55F

Description

Version:

The innovative tooth geometry permits **very high metal removal rates** combined with **smooth cutting and good guidance accuracy**. The optimised chip formation (no pointed chips) ensures good surface quality. Shank \varnothing 6 mm.

Application:

Optimised for **use on steel and steel castings**.

Shank \varnothing : 6 mm

Shape description: ball nose

Head \varnothing : 8 mm

Head length: 20 mm

Overall length: 60 mm

Shank \varnothing : 6 mm

Technical description

Toothing grit designation	coarse
Tooth type abbreviation	STEEL
Head \varnothing	8 mm
Shape description	ball nose
Overall length	60 mm
Shape	C0820
Shank \varnothing	6 mm
Head length	20 mm

Tool material	Carbide
Type of product	Burr

User data

	Suitability	V_c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
GG(G)	suitable		