



Abrasive flap disc SLTflex (ZA), mounting M14, 125 mm Ø, Grit: 60



Order data

Order number	566310 60
GTIN	4027497330447
Item class	53L

Description

Version:

The **sickle-shaped strips** (patented) are radially linked to a high-strength GRP centre. The **pad-less design** permits an **extremely large overlap between strips**. Very high coating density. M14 threaded mounting, **no clamping nut required**.

Zirconium Aluminium Oxide (ZA) with active upper layer bonding for **general-purpose use**.

Application:

For use in **inaccessible places**, contour grinding and for **grinding out of weld fillets**. Large overlap between strips permits **soft cutting**.

Technical description

Shape description	dished with overlap between strips
Grit	60
Disc Ø	125 mm
Series	SLTflex
Grinding medium code	ZA

Iron, sulphur and chlorine constituents	<0.1 %
Product name attribute	125 mm Ø
Thread	M14
optimised for material	Steel
maximum circumferential speed	80 m/s
Type of product	Abrasive flap disc

User data

	Suitability	V _c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		
dry	suitable		