

Garant**Set of grinding points coarse, AR, Number of grinding points: 10****Order data**

Order number	550200 10
GTIN	4045197239099
Item class	51E

Description**Version:**

GARANT grinding points (OSA certified and tested to DIN EN 12 413) are specially designed for hardness, bonding, grit type and grit size for the specific applications and cover a very wide application range. Minimal radial run-out ensures vibration-free grinding which is good for man, machine, and component. GARANT grinding points are generally suitable for **edge and surface grinding** and provide you with maximum material removal rates, long service life, and consistent surface finish quality of the component.

Shank Ø 6 mm × 40 mm.

Ceramic bonded grinding points in **pink electro-carborundum (AR)**. Medium-hard version.

Assortment of grinding points in the most popular shapes and sizes.

Application:

For general-purpose grinding of **unalloyed and low-alloy** steels and **cast iron**.

Recommended cutting speed 30 – 50 m/s.

Supplied with:

1 each grinding point ZY1020 / ZY1325 / ZY1632 / ZY2006 / ZY2025 / SP1320 / SP2032 / KE2032 / KU16 / KU20.

Technical description

Number of grinding points	10
Grit designation	coarse
Grinding media	Standard aluminium oxide (A)
Grinding medium code	A
Product name attribute	AR
Shank Ø	6 mm
Shaft length	40 mm
Type of product	Grinding point