

**Burr Tooth profile INOX – coarse, Carbide, Type: G1225****Order data**

Order number	547200 G1225
GTIN	4007220936894
Item class	55F

Description**Version:**

The innovative tooth geometry permits **very high metal removal rates** combined with **smooth cutting and good guidance accuracy**. Outstanding chip formation and surface results, low heat input into the material (no tempering colouration). Shank Ø 6mm.

Application:

Optimised for use on **austenitic, rust-resistant and acid-resistant steels**, soft titanium alloys and non-ferrous metals.

Technical description

Overall length	65 mm
Toothing grit designation	coarse
Head Ø	12 mm
Tooth type abbreviation	INOX
Shape	G1225
Shape description	Pointed arch
Shank Ø	6 mm
Head length	25 mm
Tool material	Carbide
Type of product	Burr

User data

	Suitability	V_c	ISO code
Alu Mg	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable only under restricted conditions		
CuZn	suitable only under restricted conditions		