

## Garant

### Mini grinding point fine, AR, Type: ZY0306



#### Order data

|              |               |
|--------------|---------------|
| Order number | 550400 ZY0306 |
| GTIN         | 4045197239129 |
| Item class   | 51E           |

#### Description

##### Version:

**GARANT grinding points** (OSA certified and tested to DIN EN 12 413) are specially designed for hardness, bonding, grit type and grit size for the specific applications and cover a very wide application range. Minimal radial run-out ensures vibration-free grinding which is good for man, machine, and component. GARANT grinding points are generally suitable for **edge and surface grinding** and provide you with maximum material removal rates, long service life, and consistent surface finish quality of the component.

Ceramic bonded grinding points in **pink aluminium oxide (AR)**. Medium-hard version.

Fine grit. Shank  $\varnothing$  3 mm, shank length 30 mm.

##### Application:

For general-purpose grinding of **unalloyed and low-alloy** steels and **cast iron**.

Recommended cutting speed 30 – 50 m/s.

#### Technical description

|                        |                              |
|------------------------|------------------------------|
| Shaft length           | 30 mm                        |
| Head $\varnothing$     | 3 mm                         |
| Grit designation       | fine                         |
| Shank $\varnothing$    | 3 mm                         |
| Head length            | 6 mm                         |
| Grinding media         | Standard aluminium oxide (A) |
| Grinding medium code   | A                            |
| Product name attribute | AR                           |

Type of product

Grinding point