

Fine thread "Go" ring gauge 6g, M × pitch: 8X0,75



Order data

| | |
|--------------|---------------|
| Order number | 486110 8X0,75 |
| GTIN | 2050001037466 |
| Item class | 48B |

Description

Version:

The ground first thread lead chamfer (from 1 mm pitch) removes contamination in the component and prevents premature fracture of the first full thread lead chamfer.

Design to **DIN 2279 – 2299**.

Application:

For metric ISO fine threads, right-hand DIN 13.

Standard:

Toleranzen und Abmaße nach **DIN ISO 1502**.

Note:

Thread gauges for threads with other pitches, Whitworth, trapezoidal, round, UNC, UNF, and NPT threads as well as left-hand threads available on request.

Technical description

| | |
|-----------------|---------|
| Thread pitch | 0.75 mm |
| Tolerance class | 6g |
| Thread | M8 |
| Calibration | L12 |

| | |
|-----------------|------------------------|
| Type of gauge | "Go" plug gauge |
| Tolerance zone | g |
| Thread type | MF |
| Standard | DIN 13 |
| Quality | 6 |
| Type of product | Thread "Go" ring gauge |

Services

| | |
|---|------------|
| DAkkS calibration Thread "Go" ring gauge maximum \varnothing 100 mm | 028640 100 |
| Calibration Thread ring gauge maximum \varnothing 20 mm | 028600 20 |