

## Garant

### Mini grinding point fine, AR, Type: ZY0610



#### Order data

Order number	550400 ZY0610
GTIN	4045197239150
Item class	51E

#### Description

##### Version:

**GARANT grinding points** (OSA certified and tested to DIN EN 12 413) are specially designed for hardness, bonding, grit type and grit size for the specific applications and cover a very wide application range. Minimal radial run-out ensures vibration-free grinding which is good for man, machine, and component. GARANT grinding points are generally suitable for **edge and surface grinding** and provide you with maximum material removal rates, long service life, and consistent surface finish quality of the component.

Ceramic bonded grinding points in **pink aluminium oxide (AR)**. Medium-hard version.

Fine grit. Shank  $\varnothing$  3 mm, shank length 30 mm.

##### Application:

For general-purpose grinding of **unalloyed and low-alloy** steels and **cast iron**.

Recommended cutting speed 30 – 50 m/s.

#### Technical description

Grit designation	fine
Head $\varnothing$	6 mm
Shaft length	30 mm
Shank $\varnothing$	3 mm
Head length	10 mm
Grinding media	Standard aluminium oxide (A)
Grinding medium code	A
Product name attribute	AR

Type of product

Grinding point