

Fine thread "Go" ring gauge 6g, M × pitch: 10X0,75



Order data

Order number	486110 10X0,75
GTIN	2050001041951
Item class	48B

Description

Version:

The ground first thread lead chamfer (from 1 mm pitch) removes contamination in the component and prevents premature fracture of the first full thread lead chamfer.

Design to **DIN 2279 – 2299**.

Application:

For metric ISO fine threads, right-hand DIN 13.

Standard:

Toleranzen und Abmaße nach **DIN ISO 1502**.

Note:

Thread gauges for threads with other pitches, Whitworth, trapezoidal, round, UNC, UNF, and NPT threads as well as left-hand threads available on request.

Technical description

Thread pitch	0.75 mm
Tolerance class	6g
Thread	M10
Calibration	L12

Tolerance zone	g
Type of gauge	"Go" plug gauge
Thread type	MF
Standard	DIN 13
Quality	6
Type of product	Thread "Go" ring gauge

Services

DAkkS calibration Thread "Go" ring gauge maximum \varnothing 100 mm	028640 100
Calibration Thread ring gauge maximum \varnothing 20 mm	028600 20