

Fine thread "Go" / "No Go" plug gauge 6H, M × pitch: 27X1,5



Order data

Order number	486100 27X1,5
GTIN	2050001675507
Item class	48B

Description

Version:

The ground first thread lead chamfer (from 1 mm pitch) removes contamination in the component and prevents premature fracture of the first full thread lead chamfer.

Design to **DIN 2279 – 2299**.

"Go" and "No Go" ends on a single handle (DIN 2240, part 1 form R). "No Go" end marked red.

Application:

For metric ISO fine threads, right-hand DIN 13.

Standard:

Toleranzen und Abmaße nach **DIN ISO 1502**.

Note:

Thread gauges for threads with other pitches, Whitworth, trapezoidal, round, UNC, UNF, and NPT threads as well as left-hand threads available on request.

Technical description

Tolerance class	6H
Thread pitch	1.5 mm
Thread	M27
Standard	DIN 13
Thread type	MF
Quality	6
Tolerance zone	H
Type of gauge	"No Go" gauge

Type of gauge	"Go" plug gauge
Calibration	L10
Type of product	Thread Go / NoGo plug gauge

Services

CalibrationGo / No Go thread plug gauge maximum Ø 60 mm	028550 60
DAkkS calibration "Go" / "No Go" thread plug gauge maximum Ø 90 mm	028590 90