


**Flap wheel for stainless steel, 120 grit, Head Ø×head width: 30X10mm****Order data**

Order number	554310 30X10
GTIN	4045197235589
Item class	52E

Description**Version:**

Flap strips bonded on to the shank of the tool.

Abrasive strips covered with **Aluminium Oxide (A)**. With **active abrasive bonding** for stainless steels

Application:

Primarily for finish grinding and polishing tasks on larger radii in tool and mould making, for vessel and machine fabrication. The abrasive strips adapt to the contours of the component.

Technical description

Grit	120
Head width	10 mm
maximum speed	25400 min ⁻¹
recommended speed	16000 min ⁻¹
Shank Ø	6 mm
Head Ø	30 mm
Grinding media	Aluminium Oxide grit (A)

Grinding medium code	A
Product name attribute	120 grit
Type of product	Flap wheel

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
INOX	suitable		
Ti	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
dry	suitable		