

Garant

Mini grinding point fine, AR, Type: ZY0810



Order data

| | |
|--------------|---------------|
| Order number | 550400 ZY0810 |
| GTIN | 4045197239174 |
| Item class | 51E |

Description

Version:

GARANT grinding points (OSA certified and tested to DIN EN 12 413) are specially designed for hardness, bonding, grit type and grit size for the specific applications and cover a very wide application range. Minimal radial run-out ensures vibration-free grinding which is good for man, machine, and component. GARANT grinding points are generally suitable for **edge and surface grinding** and provide you with maximum material removal rates, long service life, and consistent surface finish quality of the component.

Ceramic bonded grinding points in **pink aluminium oxide (AR)**. Medium-hard version.

Fine grit. Shank \varnothing 3 mm, shank length 30 mm.

Application:

For general-purpose grinding of **unalloyed and low-alloy** steels and **cast iron**.

Recommended cutting speed 30 – 50 m/s.

Technical description

| | |
|------------------------|------------------------------|
| Grit designation | fine |
| Head \varnothing | 8 mm |
| Shaft length | 30 mm |
| Shank \varnothing | 3 mm |
| Head length | 10 mm |
| Grinding media | Standard aluminium oxide (A) |
| Grinding medium code | A |
| Product name attribute | AR |

Type of product

Grinding point