



## Flap wheel (A), 80 grit, Head $\varnothing$ ×head width: 30X5mm



### Order data

Order number	554200 30X5
GTIN	4045197240637
Item class	52E

### Description

#### Version:

Flap strips bonded on to the shank of the tool.

Abrasive strips covered with **Aluminium Oxide (A)**.

#### Application:

Primarily for finish grinding and polishing tasks on larger radii in tool and mould making, for vessel and machine fabrication. The abrasive strips adapt to the contours of the component.

### Technical description

Grit	80
maximum speed	25400 min <sup>-1</sup>
recommended speed	16000 min <sup>-1</sup>
Head width	5 mm
Shank $\varnothing$	6 mm
Head $\varnothing$	30 mm
Grinding media	Aluminium Oxide grit (A)
Grinding medium code	A

Product name attribute	80 grit
Type of product	Flap wheel

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable only under restricted conditions		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
dry	suitable		