

Garant**Grinding point coarse, AR, Type: ZY2025****Order data**

| | |
|--------------|---------------|
| Order number | 550600 ZY2025 |
| GTIN | 4045197239273 |
| Item class | 51E |

Description**Version:**

GARANT grinding points (OSA certified and tested to DIN EN 12 413) are specially designed for hardness, bonding, grit type and grit size for the specific applications and cover a very wide application range. Minimal radial run-out ensures vibration-free grinding which is good for man, machine, and component. GARANT grinding points are generally suitable for **edge and surface grinding** and provide you with maximum material removal rates, long service life, and consistent surface finish quality of the component.

Ceramic bonded grinding points in **pink aluminium oxide (AR)**. Medium-hard version.

Coarse grit. Shank length 40 mm.

Application:

For general-purpose grinding of **unalloyed and low-alloy** steels and **cast iron**.

Recommended cutting speed 30 – 50 m/s.

Technical description

| | |
|----------------------|------------------------------|
| Head Ø | 20 mm |
| Grit designation | coarse |
| Shaft length | 40 mm |
| Shank Ø | 6 mm |
| Head length | 25 mm |
| Grinding media | Standard aluminium oxide (A) |
| Grinding medium code | A |

| | |
|------------------------|----------------|
| Product name attribute | AR |
| Type of product | Grinding point |