

**Fine thread “Go” / “No Go” plug gauge 6H, M × pitch: 12X1,5****Order data**

Order number	486100 12X1,5
GTIN	2050001675347
Item class	48B

**Description****Version:**

The ground first thread lead chamfer (from 1 mm pitch) removes contamination in the component and prevents premature fracture of the first full thread lead chamfer.

Design to **DIN 2279 – 2299**.

**“Go” and “No Go” ends on a single handle (DIN 2240, part 1 form R).** “No Go” end marked red.

**Application:**

For metric ISO fine threads, right-hand DIN 13.

**Standard:**

Toleranzen und Abmaße nach **DIN ISO 1502**.

**Note:**

Thread gauges for threads with other pitches, Whitworth, trapezoidal, round, UNC, UNF, and NPT threads as well as left-hand threads available on request.

**Technical description**

Thread	M12
Tolerance class	6H
Thread pitch	1.5 mm
Standard	DIN 13
Thread type	MF
Tolerance zone	H
Quality	6
Type of gauge	“No Go” gauge

Type of gauge	"Go" plug gauge
Calibration	L10
Type of product	Thread Go / NoGo plug gauge

## Services

CalibrationGo / No Go thread plug gauge maximum Ø 20 mm	028550 20
DAkkS calibration "Go" / "No Go" thread plug gauge maximum Ø 90 mm	028590 90