


HOLEX**Flap wheel (A), 120 grit, Head Ø×head width: 50X15mm****Order data**

Order number	554300 50X15
GTIN	4045197240767
Item class	52E

Description**Version:**

Flap strips bonded on to the shank of the tool.

Abrasive strips covered with **Aluminium Oxide (A)**.

Application:

Primarily for finish grinding and polishing tasks on larger radii in tool and mould making, for vessel and machine fabrication. The abrasive strips adapt to the contours of the component.

Technical description

Grit	120
maximum speed	15300 min ⁻¹
recommended speed	9000 min ⁻¹
Head width	15 mm
Shank Ø	6 mm
Head Ø	50 mm

Grinding media	Aluminium Oxide grit (A)
Grinding medium code	A
Product name attribute	120 grit
Type of product	Flap wheel

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable only under restricted conditions		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
dry	suitable		