

Garant**Flap wheel Fleece (ZA), medium, Head Ø×head width: 30X20mm****Order data**

| | |
|--------------|---------------|
| Order number | 554906 30X20 |
| GTIN | 4045197679833 |
| Item class | 51E |

Description**Version:**

Flap strips of fleece around the shank of the tool. Shank Ø 6 mm.

Especially wear-resistant and fine-structured fleece with Zirconium Aluminium Oxide (ZA). **Ideal for use on stainless steel.**

Application:

For removal of dirt and oxide layers on metals as well as for matt finishing of Cr-Ni, other stainless steels, and also non-ferrous metals.

Technical description

| | |
|----------------------|-------------------------|
| recommended speed | 7500 min ⁻¹ |
| maximum speed | 14000 min ⁻¹ |
| Head width | 20 mm |
| Shank Ø | 6 mm |
| Head Ø | 30 mm |
| Grinding medium code | ZA |
| Grit equivalent | 180 |
| Grit designation | medium |

| | |
|------------------------|------------|
| Product name attribute | medium |
| Type of product | Flap wheel |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Alu Mg | suitable only under restricted conditions | | |
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable only under restricted conditions | | |
| Steel < 67 HRC | suitable only under restricted conditions | | |
| INOX | suitable | | |
| Ti | suitable only under restricted conditions | | |
| GG(G) | suitable | | |
| CuZn | suitable | | |
| Plastic, GRP | suitable | | |
| Wood | suitable | | |
| Paint | suitable only under restricted conditions | | |
| dry | suitable | | |