

Garant**Flap wheel Fleece (ZA), medium, Head Ø×head width: 80X50mm****Order data**

Order number	554906 80X50
GTIN	4045197676092
Item class	51E

Description**Version:**

Flap strips of fleece around the shank of the tool. Shank Ø 6 mm.

Especially wear-resistant and fine-structured fleece with Zirconium Aluminium Oxide (ZA). **Ideal for use on stainless steel.**

Application:

For removal of dirt and oxide layers on metals as well as for matt finishing of Cr-Ni, other stainless steels, and also non-ferrous metals.

Technical description

maximum speed	7000 min ⁻¹
recommended speed	4000 min ⁻¹
Head width	50 mm
Shank Ø	6 mm
Head Ø	80 mm
Grinding medium code	ZA

Grit equivalent	180
Grit designation	medium
Product name attribute	medium
Type of product	Flap wheel

User data

	Suitability	V _c	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable only under restricted conditions		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Paint	suitable only under restricted conditions		
dry	suitable		