


**Flap wheel Fleece / cloth, coarse, Head Ø×head width: 40X20mm****Order data**

Order number	554910 40X20
GTIN	4045197241078
Item class	52E

**Description****Version:**

Flap strips bonded on to the shank of the tool. Fleece is combined with abrasive cloth to **increase the abrasive effect** of the fleece. Shank Ø 6 mm.

**Application:**

For removal of dirt and oxide layers on metals as well as for matt finishing of Cr-Ni, other stainless steels, and also non-ferrous metals.

**Technical description**

maximum speed	14000 min <sup>-1</sup>
recommended speed	7500 min <sup>-1</sup>
Head width	20 mm
Shank Ø	6 mm
Head Ø	40 mm
Grinding medium code	A
Grit equivalent	100 / 80
Grit designation	coarse

Product name attribute	coarse
Type of product	Flap wheel

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable only under restricted conditions		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Paint	suitable only under restricted conditions		
dry	suitable		