




Flap wheel for stainless steel, 150 grit, Head \varnothing ×head width: 30X10mm



Order data

Order number	554410 30X10
GTIN	4045197377654
Item class	52E

Description

Version:

Flap strips bonded on to the shank of the tool.

Abrasive strips covered with **Aluminium Oxide (A)**. With **active abrasive bonding** for stainless steels

Application:

Primarily for finish grinding and polishing tasks on larger radii in tool and mould making, for vessel and machine fabrication. The abrasive strips adapt to the contours of the component.

Technical description

recommended speed	16000 min ⁻¹
Grit	150
maximum speed	25400 min ⁻¹
Head width	10 mm
Shank \varnothing	6 mm
Head \varnothing	30 mm
Grinding media	Aluminium Oxide grit (A)

Grinding medium code	A
Product name attribute	150 grit
Type of product	Flap wheel

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
INOX	suitable		
Ti	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
dry	suitable		