

**Garant****Grinding point coarse, AN, Type: ZY1632****Order data**

Order number	551600 ZY1632
GTIN	4045197239693
Item class	51E

**Description****Version:**

**GARANT grinding points** (OSA certified and tested to DIN EN 12 413) are specially designed for hardness, bonding, grit type and grit size for the specific applications and cover a very wide application range. Minimal radial run-out ensures vibration-free grinding which is good for man, machine, and component. GARANT grinding points are generally suitable for **edge and surface grinding** and provide you with maximum material removal rates, long service life, and consistent surface finish quality of the component.

Grinding point in **standard aluminium oxide (AN)** in coarse grit and synthetic resin bonding. Shank length 40 mm.

**Application:**

For grinding of **high-alloy** steel, stainless steel and **cast iron**.  
Recommended cutting speed 40 – 50 m/s.

**Technical description**

Shaft length	40 mm
Grit designation	coarse

Head Ø	16 mm
Shank Ø	6 mm
Head length	32 mm
Grinding media	Standard aluminium oxide (A)
Grinding medium code	A
Product name attribute	AN
Type of product	Grinding point