

Garant**Grinding point coarse, AN, Type: ZY2025****Order data**

| | |
|--------------|---------------|
| Order number | 551600 ZY2025 |
| GTIN | 4045197239709 |
| Item class | 51E |

Description**Version:**

GARANT grinding points (OSA certified and tested to DIN EN 12 413) are specially designed for hardness, bonding, grit type and grit size for the specific applications and cover a very wide application range. Minimal radial run-out ensures vibration-free grinding which is good for man, machine, and component. GARANT grinding points are generally suitable for **edge and surface grinding** and provide you with maximum material removal rates, long service life, and consistent surface finish quality of the component.

Grinding point in **standard aluminium oxide (AN)** in coarse grit and synthetic resin bonding. Shank length 40 mm.

Application:

For grinding of **high-alloy** steel, stainless steel and **cast iron**.
Recommended cutting speed 40 – 50 m/s.

Technical description

| | |
|------------------|--------|
| Shaft length | 40 mm |
| Grit designation | coarse |

| | |
|------------------------|------------------------------|
| Head Ø | 20 mm |
| Shank Ø | 6 mm |
| Head length | 25 mm |
| Grinding media | Standard aluminium oxide (A) |
| Grinding medium code | A |
| Product name attribute | AN |
| Type of product | Grinding point |