


**Fibre disc Aluminium Oxide (A), Ø 125 mm, Grit: 120****Order data**

Order number	566510 120
GTIN	4045197527059
Item class	52M

**Description****Version:**

Tear-resistant but very flexible **vulcanised fibre**. Bore diameter 22.23 mm and crossed slots.  
**HOLEX universal fibre disc** for grinding all metals. Grit type: **Aluminium oxide (A)**.

**Application:**

Limited to maximum 80 m/s circumferential speed with backing pads No. 566650 / 566670 on angle grinders. For **grinding flat and curved surfaces** with a high degree of **flexibility**.

**Technical description**

Grit	120
Disc Ø	125 mm
Grinding media	Regular aluminium oxide (A)
Grinding medium code	A
Grinding media backing	Vulcanised fibre
Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	Ø 125 mm
Adapter	Roloc™ quick-change system

Bore Ø	22.23 mm
suitable for quick-change system	Roloc™
optimised for material	Steel
maximum circumferential speed	80 m/s
maximum speed	12200 min <sup>-1</sup>
Type of product	Fibre disc

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
INOX	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
dry	suitable		

## Accessories

ISO backing padflexible/smooth External Ø 117 mm	566650 117
Backing padhard/ribbed External Ø 125 mm	566672 125
ISO backing padmedium hard/ribbed External Ø 117 mm	566670 117