

Garant**Grinding point coarse, AW-AN, Type: ZY1632****Order data**

Order number	551700 ZY1632
GTIN	4045197239747
Item class	51E

Description**Version:**

GARANT grinding points (OSA certified and tested to DIN EN 12 413) are specially designed for hardness, bonding, grit type and grit size for the specific applications and cover a very wide application range. Minimal radial run-out ensures vibration-free grinding which is good for man, machine, and component. GARANT grinding points are generally suitable for **edge and surface grinding** and provide you with maximum material removal rates, long service life, and consistent surface finish quality of the component.

Grinding point in special quality **mixed aluminium oxide**, 30 grit (coarse), and ceramic bonding. Shank \varnothing 6 mm, shank length 40 mm.

Application:

For coarse grinding of **cast iron** and **stainless steel**. Recommended cutting speed 40 – 50 m/s.

Technical description

Head \varnothing	16 mm
Shaft length	40 mm
Grit designation	coarse

Shank Ø	6 mm
Head length	32 mm
Grinding media	Standard aluminium oxide (A)
Grinding medium code	A
Product name attribute	AW-AN
Type of product	Grinding point